



Welcome

Shuh-Ren Lai

[Home](#) | [Help](#) | [Contact](#) | [Logout](#)

search:

[My Site](#)

[Substances](#)

Know-How

- [Glossary](#)
- [Regulations](#)
- [Air-Emission](#)
- [Water-Emission](#)
- [Substance Tracking](#)
- [BAT](#)

Bluesign

- [About Us](#)
- [News](#)
- [Legal](#)
- [Links](#)
- [General Info](#)
- [Downloads](#)
- [Conference](#)

Downloads

Video

Photos

T&T Industries Corporation

supporter: T&T Industries Corporation
Kui-Chun Lin
No. 3, Guojian 1st Road, Guanyin Township
Taoyuan County 328

Taiwan

Phone: +886 3 4831666 Ext. 206

Fax: +886 3 4832666

Email: ccp6659@tntind.com.tw

URL: www.tntind.com.tw

segment: Textiles

range: Taicron (D)

type: 10.4 Disperse dyes

Description

edit text

Features

edit list

[Dyestuffs and Aftertreatment Agents](#)

[Taiacryl \(D\)](#)

[Taicron \(D\)](#)

bluesign® approved components

| name | rating class | details |
|---|--------------|---------|
| TAICRON BLACK ASP-RST | B - C | |
| TAICRON BLACK ASP-RT | B - C | |
| TAICRON BLACK A-T | B - C | |
| TAICRON BLACK AXF-T | B - C | |
| TAICRON BLACK FD-BST | B - C | |
| TAICRON BLACK HW-T NEW | B - C | |
| TAICRON BLACK R-MBT | B - C | |
| TAICRON BLACK SE-EXNT ECO 300% | B - C | |
| TAICRON BLACK SF-EX01 200% | B - C | |
| TAICRON BLACK SF-GT 300% | B - C | |
| TAICRON BLACK SF-GT ECO 150% LIQ. | B - C | |
| TAICRON BLACK SF-GT ECO 300% | B - C | |
| TAICRON BLACK SP-2BT | B - C | |
| TAICRON BLACK SP-2RT | B - C | |
| TAICRON BLACK SP-AST | B - C | |
| TAICRON BLACK SP-GT | B - C | |
| TAICRON BLACK SP-RST | B - C | |
| TAICRON BLACK SP-RT H/C | B - C | |
| TAICRON BLACK XF-T | A - B - C | |
| TAICRON BLUE 2RHW-T | B - C | |
| TAICRON BLUE E-ACT | B - C | |
| TAICRON BLUE FBL-T | B - C | |
| TAICRON BLUE KBHW-T | B - C | |
| TAICRON BLUE SE-UNT 200% | B - C | |
| TAICRON BLUE SE-UNT GRAN | B - C | |
| TAICRON BLUE SF-3RT 200% | B - C | |

| | | | | | |
|--|---|---|---|---|---|
| TAICRON BLUE SP-3GT | | B | - | C | |
| TAICRON BLUE SRF-T H/C | | B | - | C | |
| TAICRON BLUE XF-T | | B | - | C | |
| TAICRON BRILL. BLUE SE-GLT 200% | A | - | B | - | C |
| TAICRON BRILL. RED XF-T | | B | - | C | |
| TAICRON BRILL. SCARLET HSF-T | | B | - | C | |
| TAICRON CRIMSON XFN-T | A | - | B | - | C |
| TAICRON CRIMSON XF-T | | B | - | C | |
| TAICRON CYANINE BN-T NEW | A | - | B | - | C |
| TAICRON DEEP RED ASP-WT | | B | - | C | |
| TAICRON DEEP RED SP-WT | A | - | B | - | C |
| TAICRON GOLDEN YELLOW SP-RST | | B | - | C | |
| TAICRON NAVY BLUE AXF-T | | B | - | C | |
| TAICRON NAVY BLUE HW-T ECO | | B | - | C | |
| TAICRON NAVY BLUE SE-UNT 200% | | B | - | C | |
| TAICRON NAVY BLUE SF-GT ECO 300% | | B | - | C | |
| TAICRON NAVY BLUE SP-BRST | | B | - | C | |
| TAICRON NAVY BLUE SP-BT | | B | - | C | |
| TAICRON NAVY BLUE SP-GT | | B | - | C | |
| TAICRON NAVY BLUE XF-T | A | - | B | - | C |
| TAICRON ORANGE E-3RT 200% GRAN | | B | - | C | |
| TAICRON ORANGE SF-GFT 200% NEW | | B | - | C | |
| TAICRON ORANGE SF-RT 200% | | B | - | C | |
| TAICRON RED BWF-T | A | - | B | - | C |
| TAICRON RED E-ACT | | B | - | C | |
| TAICRON RED E-FBNT 200% | | B | - | C | |
| TAICRON RED KXF-T | A | - | B | - | C |
| TAICRON RED SBS | A | - | B | - | C |
| TAICRON RED SP-2BST | | B | - | C | |
| TAICRON RED SP-2RT | | B | - | C | |
| TAICRON RED XF-T | A | - | B | - | C |
| TAICRON RUBINE AH | | B | - | C | |
| TAICRON RUBINE HW-T | | B | - | C | |
| TAICRON RUBINE SE-GLNT 200% GRAN | | B | - | C | |
| TAICRON RUBINE SE-UNT | | B | - | C | |
| TAICRON RUBINE SP-BSNT | | B | - | C | |
| TAICRON RUBINE SP-BST | | B | - | C | |
| TAICRON RUBINE XF-T | | B | - | C | |
| TAICRON SCARLET XFN-T | A | - | B | - | C |
| TAICRON TURQUOISE BLUE XF-T | | B | - | C | |
| TAICRON VIOLET SF-3RLT 200% | | B | - | C | |
| TAICRON YELLOW 5GNT | | B | - | C | |
| TAICRON YELLOW BROWN ECO 200% | | B | - | C | |
| TAICRON YELLOW BROWN SP-3RT | | B | - | C | |
| TAICRON YELLOW BROWN XF-T | | B | - | C | |
| TAICRON YELLOW E-ACT | | B | - | C | |
| TAICRON YELLOW HW-T | | B | - | C | |
| TAICRON YELLOW SE-4GT 200% | A | - | B | - | C |
| TAICRON YELLOW SE-5GT | | B | - | C | |
| TAICRON YELLOW SE-UNT 200% | | B | - | C | |
| TAICRON YELLOW SF-6GT 200% NEW | | B | - | C | |
| TAICRON YELLOW SP-HGT | | B | - | C | |

Disable Edit Mode